

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205166

Luminaire Tested: **LSR6B10D010BZ EC6B10208027 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205166
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208027 6LBWLI1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1027.5 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205166

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P205166

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92																												
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																												
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76																												
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69																												
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63																												
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57																												
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																												
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																												
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44																												
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205166

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.9	6.0
10°-20°	186.1	18.1
20°-30°	280.6	27.3
30°-40°	287.2	27.9
40°-50°	167.3	16.3
50°-60°	38.4	3.7
60°-70°	4.7	0.5
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	528.6	51.4
0°-40°	815.8	79.4
0°-60°	1021.6	99.4
0°-90°	1027.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1027.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	642	
5°	645	62
15°	659	186
25°	615	281
35°	466	287
45°	216	167
55°	37	38
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P205166

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBWLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	641.9
2.5°	640.7
5°	645.4
7.5°	650.1
10°	655.9
12.5°	657.1
15°	659.4
17.5°	657.1
20°	651.2
22.5°	632.6
25°	615.1
27.5°	587.2
30°	551.0
32.5°	513.8
35°	466.0
37.5°	412.4
40°	353.0
42.5°	286.6
45°	215.5
47.5°	150.3
50°	99.0
52.5°	62.9
55°	37.3
57.5°	19.8
60°	10.5
62.5°	5.8
65°	3.5
67.5°	3.5
70°	2.3
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)