

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203753

Luminaire Tested: **LSR6B20D010BZ EC6B10208040 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10208040 6LBNWH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1422.1 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203753

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203753

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94																																			
	2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																																			
	3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																																			
	4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79																																			
	5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																																			
	6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70																																			
	7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66																																			
	8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63																																			
	9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60																																			
	10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57																																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203753

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.3	16.6
10°-20°	454.1	31.9
20°-30°	412.9	29.0
30°-40°	250.3	17.6
40°-50°	57.0	4.0
50°-60°	7.3	0.5
60°-70°	3.3	0.2
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1103.3	77.6
0°-40°	1353.6	95.2
0°-60°	1417.9	99.7
0°-90°	1422.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1422.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2792	
5°	2632	236
15°	1636	454
25°	895	413
35°	397	250
45°	63	57
55°	7	7
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203753

CATALOG NUMBER: LSR6B20D010BZ EC6B10208040 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2792.0
2.5°	2758.1
5°	2632.3
7.5°	2429.1
10°	2170.2
12.5°	1901.7
15°	1635.5
17.5°	1393.6
20°	1190.3
22.5°	1025.8
25°	895.2
27.5°	779.0
30°	665.3
32.5°	532.3
35°	396.8
37.5°	278.2
40°	183.9
42.5°	113.7
45°	62.9
47.5°	29.0
50°	12.1
52.5°	9.7
55°	7.3
57.5°	7.3
60°	4.8
62.5°	4.8
65°	2.4
67.5°	2.4
70°	2.4
72.5°	2.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)