

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202798

Luminaire Tested: **LSR6B10D010BZ EC6B10208027 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208027 6LBWWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 929.7 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202798

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202798

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202798

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.5	6.0
10°-20°	165.0	17.8
20°-30°	248.5	26.7
30°-40°	254.0	27.3
40°-50°	154.3	16.6
50°-60°	43.5	4.7
60°-70°	6.6	0.7
70°-80°	2.1	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	469.0	50.4
0°-40°	723.0	77.8
0°-60°	920.8	99.0
0°-90°	929.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	929.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	577	
5°	580	56
15°	584	165
25°	542	248
35°	412	254
45°	198	154
55°	43	43
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P202798

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	577.4
2.5°	577.4
5°	579.8
7.5°	583.3
10°	583.3
12.5°	585.6
15°	584.4
17.5°	582.1
20°	573.9
22.5°	562.3
25°	542.4
27.5°	520.3
30°	489.9
32.5°	453.8
35°	411.8
37.5°	365.1
40°	311.5
42.5°	255.5
45°	198.3
47.5°	147.0
50°	103.8
52.5°	70.0
55°	43.2
57.5°	25.7
60°	12.8
62.5°	8.2
65°	5.8
67.5°	4.7
70°	3.5
72.5°	2.3
75°	2.3
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)