

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203244

Luminaire Tested: **LSR6B20D010BZ EC6B10209040 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203244
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209040 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1292.3 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203244

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203244

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203244

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.9	9.0
10°-20°	302.5	23.4
20°-30°	392.0	30.3
30°-40°	291.0	22.5
40°-50°	122.8	9.5
50°-60°	43.6	3.4
60°-70°	16.8	1.3
70°-80°	5.8	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.5	62.8
0°-40°	1102.5	85.3
0°-60°	1269.0	98.2
0°-90°	1292.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1292.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1279	
5°	1251	117
15°	1080	303
25°	869	392
35°	461	291
45°	151	123
55°	46	44
65°	17	17
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P203244

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1279.0
2.5°	1275.3
5°	1251.3
7.5°	1216.2
10°	1173.8
12.5°	1127.6
15°	1079.7
17.5°	1026.1
20°	978.1
22.5°	928.3
25°	869.3
27.5°	788.1
30°	692.1
32.5°	579.5
35°	461.4
37.5°	361.7
40°	275.0
42.5°	204.9
45°	151.3
47.5°	110.7
50°	81.2
52.5°	60.9
55°	46.1
57.5°	35.1
60°	27.7
62.5°	20.3
65°	16.6
67.5°	12.9
70°	9.2
72.5°	7.4
75°	5.5
77.5°	3.7
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)