

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35319

Luminaire Tested: **LSR6B10D010BZ EC6B10209027 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35319
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209027 6LBMGPH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 495.2 lumens
Efficiency: N/A
Efficacy: 51.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35319

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P35319

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33664
5°	33203
10°	31666
15°	29583
20°	27632
25°	25051
30°	20491
35°	14017
40°	8346
45°	4521
50°	2233
55°	1365
60°	913
65°	617
70°	382
75°	252
80°	376
85°	0



TEST NUMBER: P35319

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	9.6
10°-20°	123.0	24.8
20°-30°	156.7	31.6
30°-40°	110.8	22.4
40°-50°	40.4	8.2
50°-60°	11.2	2.3
60°-70°	4.1	0.8
70°-80°	1.4	0.3
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.1	66.1
0°-40°	437.9	88.4
0°-60°	489.5	98.9
0°-90°	495.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	495.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	516	
5°	507	47
15°	438	123
25°	348	157
35°	176	111
45°	49	40
55°	12	11
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P35319

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	516
2.5°	514
5°	507
7.5°	493
10°	478
12.5°	458
15°	438
17.5°	418
20°	398
22.5°	374
25°	348
27.5°	312
30°	272
32.5°	224
35°	176
37.5°	134
40°	98
42.5°	71
45°	49
47.5°	33
50°	22
52.5°	15
55°	12
57.5°	9
60°	7
62.5°	5
65°	4
67.5°	3
70°	2
72.5°	2
75°	1
77.5°	1
80°	1
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)