

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203141

Luminaire Tested: **LSR6B20D010BZ EC6B10209040 6LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203141  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10209040 6LBWMW1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1671.2 lumens  
Efficiency: N/A  
Efficacy: 80.3 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203141

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203141

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			34

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203141

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.4	5.3
10°-20°	247.9	14.8
20°-30°	357.1	21.4
30°-40°	370.8	22.2
40°-50°	274.1	16.4
50°-60°	163.7	9.8
60°-70°	99.5	6.0
70°-80°	54.5	3.3
80°-90°	15.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	693.4	41.5
0°-40°	1064.1	63.7
0°-60°	1502.0	89.9
0°-90°	1671.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1671.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	938	
5°	932	88
15°	880	248
25°	778	357
35°	598	371
45°	353	274
55°	178	164
65°	99	100
75°	51	54
85°	12	15
90°	0	



TEST NUMBER: P203141

CATALOG NUMBER: LSR6B20D010BZ EC6B10209040 6LBWMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	938.5
2.5°	938.5
5°	932.4
7.5°	924.3
10°	912.1
12.5°	897.9
15°	879.7
17.5°	859.4
20°	839.2
22.5°	810.8
25°	778.3
27.5°	743.9
30°	699.3
32.5°	654.7
35°	598.0
37.5°	539.2
40°	474.3
42.5°	411.5
45°	352.7
47.5°	300.0
50°	253.4
52.5°	212.8
55°	178.4
57.5°	152.0
60°	129.7
62.5°	113.5
65°	99.3
67.5°	87.2
70°	75.0
72.5°	62.8
75°	50.7
77.5°	40.5
80°	30.4
82.5°	22.3
85°	12.2
87.5°	6.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)