

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204998

Luminaire Tested: **LSR6B20D010BZ EC6B10209050 6LBSCMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204998  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10209050 6LBCSMMS1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1826.7 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204998

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P204998

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204998

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	4.3
10°-20°	221.8	12.1
20°-30°	324.0	17.7
30°-40°	370.6	20.3
40°-50°	356.1	19.5
50°-60°	275.0	15.1
60°-70°	153.5	8.4
70°-80°	44.7	2.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	624.9	34.2
0°-40°	995.5	54.5
0°-60°	1626.6	89.0
0°-90°	1826.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1826.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	839	
5°	832	79
15°	787	222
25°	704	324
35°	593	371
45°	464	356
55°	308	275
65°	154	153
75°	39	45
85°	1	2
90°	0	



TEST NUMBER: P204998

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	838.9
2.5°	838.9
5°	831.8
7.5°	828.2
10°	816.4
12.5°	802.2
15°	786.9
17.5°	771.5
20°	749.1
22.5°	731.4
25°	704.2
27.5°	677.0
30°	649.8
32.5°	622.7
35°	593.1
37.5°	563.6
40°	529.3
42.5°	498.6
45°	464.3
47.5°	425.3
50°	388.7
52.5°	348.5
55°	308.4
57.5°	267.0
60°	228.0
62.5°	189.0
65°	153.6
67.5°	120.5
70°	89.8
72.5°	62.6
75°	39.0
77.5°	20.1
80°	7.1
82.5°	2.4
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)