

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205472

Luminaire Tested: **LSR6B10D010BZ EC6B10208030 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208030 6LBMGPH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 593.1 lumens
Efficiency: N/A
Efficacy: 59.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205472

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205472

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93						93													
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86						86													
3	102	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79						79													
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73						73													
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68						68													
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63						63													
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59						59													
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55						55													
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51						51													
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48						48													

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205472

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	9.6
10°-20°	147.3	24.8
20°-30°	187.7	31.6
30°-40°	132.7	22.4
40°-50°	48.4	8.2
50°-60°	13.4	2.3
60°-70°	4.9	0.8
70°-80°	1.7	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	391.8	66.1
0°-40°	524.5	88.4
0°-60°	586.4	98.9
0°-90°	593.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	593.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	618	
5°	607	57
15°	525	147
25°	417	188
35°	211	133
45°	59	48
55°	14	13
65°	5	5
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P205472

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	618.0
2.5°	615.6
5°	607.3
7.5°	590.5
10°	572.5
12.5°	548.6
15°	524.6
17.5°	500.7
20°	476.7
22.5°	448.0
25°	416.8
27.5°	373.7
30°	325.8
32.5°	268.3
35°	210.8
37.5°	160.5
40°	117.4
42.5°	85.0
45°	58.7
47.5°	39.5
50°	26.4
52.5°	18.0
55°	14.4
57.5°	10.8
60°	8.4
62.5°	6.0
65°	4.8
67.5°	3.6
70°	2.4
72.5°	2.4
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)