

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204138

Luminaire Tested: **LSR6B10D010BZ EC6B10208030 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204138
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208030 6LBSH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1107.0 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204138

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204138

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204138

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	4.9
10°-20°	147.4	13.3
20°-30°	204.7	18.5
30°-40°	223.4	20.2
40°-50°	208.4	18.8
50°-60°	158.2	14.3
60°-70°	86.6	7.8
70°-80°	23.8	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	406.3	36.7
0°-40°	629.7	56.9
0°-60°	996.3	90.0
0°-90°	1107.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1107.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	579	
5°	574	54
15°	525	147
25°	445	205
35°	357	223
45°	271	208
55°	177	158
65°	86	87
75°	21	24
85°	0	0
90°	0	



TEST NUMBER: P204138

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	579.0
2.5°	579.0
5°	574.1
7.5°	566.8
10°	555.8
12.5°	541.2
15°	525.3
17.5°	505.8
20°	487.6
22.5°	465.6
25°	444.9
27.5°	424.2
30°	401.0
32.5°	379.1
35°	357.1
37.5°	335.2
40°	314.5
42.5°	292.5
45°	270.6
47.5°	248.7
50°	224.3
52.5°	201.1
55°	176.7
57.5°	153.6
60°	130.4
62.5°	107.3
65°	86.5
67.5°	67.0
70°	50.0
72.5°	34.1
75°	20.7
77.5°	9.8
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)