

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203657

Luminaire Tested: **LSR6B20D010BZ EC6B10209050 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209050 6LBNH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1117.1 lumens
Efficiency: N/A
Efficacy: 53.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203657

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203657

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54																			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203657

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.8	11.5
10°-20°	307.1	27.5
20°-30°	351.8	31.5
30°-40°	236.4	21.2
40°-50°	67.5	6.0
50°-60°	16.5	1.5
60°-70°	6.3	0.6
70°-80°	2.4	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.7	70.5
0°-40°	1024.1	91.7
0°-60°	1108.2	99.2
0°-90°	1117.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1117.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1432	
5°	1391	129
15°	1102	307
25°	768	352
35°	377	236
45°	77	68
55°	18	17
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203657

CATALOG NUMBER: LSR6B20D010BZ EC6B10209050 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1432.1
2.5°	1421.9
5°	1391.3
7.5°	1336.3
10°	1269.1
12.5°	1183.5
15°	1102.1
17.5°	1016.5
20°	930.9
22.5°	849.5
25°	768.0
27.5°	692.6
30°	605.0
32.5°	488.9
35°	376.9
37.5°	275.0
40°	189.4
42.5°	124.3
45°	77.4
47.5°	46.9
50°	28.5
52.5°	22.4
55°	18.3
57.5°	14.3
60°	10.2
62.5°	8.1
65°	6.1
67.5°	4.1
70°	4.1
72.5°	2.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)