

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204903

Luminaire Tested: **LSR6B30D010BZ EC6B30509024 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509024 6LBCSMB1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1981.7 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204903

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204903

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88						88													
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75						75													
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65						65													
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56						56													
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49						49													
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43						43													
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39						39													
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35						35													
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31						31													
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28						28													

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204903

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	4.0
10°-20°	225.5	11.4
20°-30°	339.0	17.1
30°-40°	402.2	20.3
40°-50°	398.0	20.1
50°-60°	312.6	15.8
60°-70°	175.3	8.8
70°-80°	49.2	2.5
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	643.6	32.5
0°-40°	1045.8	52.8
0°-60°	1756.4	88.6
0°-90°	1981.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1981.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	837	
5°	835	79
15°	800	225
25°	736	339
35°	645	402
45°	518	398
55°	352	313
65°	175	175
75°	43	49
85°	0	1
90°	0	



TEST NUMBER: P204903

CATALOG NUMBER: LSR6B30D010BZ EC6B30509024 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	836.8
2.5°	833.9
5°	835.4
7.5°	828.3
10°	819.7
12.5°	809.8
15°	799.8
17.5°	787.1
20°	770.0
22.5°	753.0
25°	735.9
27.5°	717.4
30°	693.3
32.5°	669.1
35°	645.0
37.5°	616.6
40°	583.9
42.5°	552.6
45°	518.5
47.5°	480.2
50°	440.4
52.5°	395.0
55°	352.3
57.5°	304.0
60°	258.6
62.5°	217.4
65°	174.7
67.5°	137.8
70°	102.3
72.5°	69.6
75°	42.6
77.5°	21.3
80°	5.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)