

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204251

Luminaire Tested: **LSR6B10D010BZ EC6B10209730 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209730 6LBSWH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 830.7 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204251

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204251

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204251

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	5.5
10°-20°	118.3	14.2
20°-30°	154.7	18.6
30°-40°	163.8	19.7
40°-50°	152.8	18.4
50°-60°	115.7	13.9
60°-70°	62.7	7.5
70°-80°	16.8	2.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	318.7	38.4
0°-40°	482.5	58.1
0°-60°	750.9	90.4
0°-90°	830.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	830.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	495	
5°	488	46
15°	423	118
25°	336	155
35°	262	164
45°	199	153
55°	130	116
65°	63	63
75°	14	17
85°	0	0
90°	0	



TEST NUMBER: P204251

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	495.4
2.5°	493.6
5°	488.1
7.5°	476.3
10°	460.9
12.5°	442.7
15°	422.7
17.5°	400.0
20°	380.0
22.5°	357.2
25°	336.3
27.5°	315.4
30°	295.4
32.5°	278.2
35°	261.8
37.5°	245.4
40°	230.0
42.5°	214.5
45°	199.1
47.5°	181.8
50°	164.5
52.5°	147.3
55°	130.0
57.5°	111.8
60°	94.5
62.5°	78.2
65°	62.7
67.5°	48.2
70°	35.5
72.5°	24.5
75°	14.5
77.5°	6.4
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)