

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202501

Luminaire Tested: **LSR6B10D010BZ EC6B10209730 6LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202501  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209730 6LBSWMH1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 833.6 lumens  
Efficiency: N/A  
Efficacy: 84.2 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202501

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202501

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88																			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47																			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42																			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38																			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35																			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202501

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.6	5.4
10°-20°	116.6	14.0
20°-30°	154.6	18.5
30°-40°	164.9	19.8
40°-50°	154.1	18.5
50°-60°	117.5	14.1
60°-70°	63.9	7.7
70°-80°	17.1	2.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.8	37.9
0°-40°	480.7	57.7
0°-60°	752.3	90.3
0°-90°	833.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	833.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	482	
5°	475	45
15°	416	117
25°	336	155
35°	264	165
45°	201	154
55°	132	118
65°	64	64
75°	15	17
85°	0	0
90°	0	



TEST NUMBER: P202501

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	482.1
2.5°	480.5
5°	475.4
7.5°	464.7
10°	452.5
12.5°	435.1
15°	415.7
17.5°	396.3
20°	375.3
22.5°	355.4
25°	336.5
27.5°	316.6
30°	297.7
32.5°	279.3
35°	263.5
37.5°	247.7
40°	231.3
42.5°	216.5
45°	200.7
47.5°	183.3
50°	167.0
52.5°	149.6
55°	132.3
57.5°	113.4
60°	96.0
62.5°	79.7
65°	63.8
67.5°	49.5
70°	36.3
72.5°	25.0
75°	14.8
77.5°	6.6
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)