

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204795

Luminaire Tested: **LSR6B30D010BZ EC6B30508027 6LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204795  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30508027 6LBCSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3104.7 lumens  
Efficiency: N/A  
Efficacy: 110.9 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204795

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204795

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204795

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	120.1	3.9
10°-20°	342.0	11.0
20°-30°	514.5	16.6
30°-40°	609.8	19.6
40°-50°	606.8	19.5
50°-60°	489.2	15.8
60°-70°	296.0	9.5
70°-80°	109.9	3.5
80°-90°	16.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	976.7	31.5
0°-40°	1586.5	51.1
0°-60°	2682.5	86.4
0°-90°	3104.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3104.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1268	
5°	1262	120
15°	1212	342
25°	1118	515
35°	976	610
45°	790	607
55°	546	489
65°	297	296
75°	100	110
85°	13	16
90°	0	



TEST NUMBER: P204795

CATALOG NUMBER: LSR6B30D010BZ EC6B30508027 6LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1268.1
2.5°	1268.1
5°	1262.4
7.5°	1258.7
10°	1247.4
12.5°	1228.6
15°	1211.6
17.5°	1192.8
20°	1170.2
22.5°	1147.7
25°	1117.6
27.5°	1085.6
30°	1049.8
32.5°	1016.0
35°	976.5
37.5°	935.1
40°	886.1
42.5°	839.1
45°	790.2
47.5°	735.6
50°	675.4
52.5°	613.3
55°	545.6
57.5°	485.4
60°	417.7
62.5°	357.5
65°	297.3
67.5°	240.8
70°	188.1
72.5°	141.1
75°	99.7
77.5°	64.0
80°	37.6
82.5°	22.6
85°	13.2
87.5°	5.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)