

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203521

Luminaire Tested: **LSR6B10D010BZ EC6B10208035 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208035 6LBMMW1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 873.6 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203521

CATALOG NUMBER: LSR6B10D010BZ EC6B10208035 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203521

CATALOG NUMBER: LSR6B10D010BZ EC6B10208035 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89																			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71																			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64																			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58																			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53																			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48																			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41																			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203521

CATALOG NUMBER: LSR6B10D010BZ EC6B10208035 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.2	6.9
10°-20°	161.3	18.5
20°-30°	216.6	24.8
30°-40°	177.6	20.3
40°-50°	106.7	12.2
50°-60°	70.9	8.1
60°-70°	47.5	5.4
70°-80°	25.6	2.9
80°-90°	7.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.1	50.1
0°-40°	615.7	70.5
0°-60°	793.3	90.8
0°-90°	873.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	873.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	652	
5°	641	60
15°	575	161
25°	477	217
35°	282	178
45°	135	107
55°	78	71
65°	48	48
75°	24	26
85°	6	7
90°	0	



TEST NUMBER: P203521

CATALOG NUMBER: LSR6B10D010BZ EC6B10208035 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	651.8
2.5°	647.0
5°	641.0
7.5°	627.7
10°	612.1
12.5°	592.8
15°	574.7
17.5°	553.0
20°	531.3
22.5°	507.2
25°	477.1
27.5°	441.0
30°	392.8
32.5°	338.6
35°	281.9
37.5°	233.7
40°	192.8
42.5°	160.2
45°	134.9
47.5°	114.5
50°	100.0
52.5°	88.0
55°	78.3
57.5°	69.9
60°	62.7
62.5°	54.2
65°	48.2
67.5°	41.0
70°	34.9
72.5°	28.9
75°	24.1
77.5°	19.3
80°	14.5
82.5°	10.8
85°	6.0
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)