

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205168

Luminaire Tested: **LSR6B10D010BZ EC6B10208035 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208035 6LBWL1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1100.6 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205168

CATALOG NUMBER: LSR6B10D010BZ EC6B10208035 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205168

CATALOG NUMBER: LSR6B10D010BZ EC6B10208035 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205168

CATALOG NUMBER: LSR6B10D010BZ EC6B10208035 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.3	6.0
10°-20°	199.4	18.1
20°-30°	300.6	27.3
30°-40°	307.6	28.0
40°-50°	179.2	16.3
50°-60°	41.2	3.7
60°-70°	5.0	0.5
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	566.3	51.5
0°-40°	873.9	79.4
0°-60°	1094.3	99.4
0°-90°	1100.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1100.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	688	
5°	691	66
15°	706	199
25°	659	301
35°	499	308
45°	231	179
55°	40	41
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P205168

CATALOG NUMBER: LSR6B10D010BZ EC6B10208035 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	687.6
2.5°	686.4
5°	691.4
7.5°	696.4
10°	702.6
12.5°	703.8
15°	706.3
17.5°	703.8
20°	697.6
22.5°	677.6
25°	658.9
27.5°	629.0
30°	590.3
32.5°	550.3
35°	499.2
37.5°	441.8
40°	378.1
42.5°	307.0
45°	230.9
47.5°	161.0
50°	106.1
52.5°	67.4
55°	39.9
57.5°	21.2
60°	11.2
62.5°	6.2
65°	3.7
67.5°	3.7
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)