

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203213

Luminaire Tested: **LSR6B10D010BZ EC6B10208040 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208040 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 804.8 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203213

CATALOG NUMBER: LSR6B10D010BZ EC6B10208040 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203213

CATALOG NUMBER: LSR6B10D010BZ EC6B10208040 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																												
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																												
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78																												
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																												
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																												
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																												
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																												
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																												
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																												
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203213

CATALOG NUMBER: LSR6B10D010BZ EC6B10208040 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	9.0
10°-20°	188.4	23.4
20°-30°	244.1	30.3
30°-40°	181.3	22.5
40°-50°	76.5	9.5
50°-60°	27.1	3.4
60°-70°	10.4	1.3
70°-80°	3.6	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	505.4	62.8
0°-40°	686.6	85.3
0°-60°	790.3	98.2
0°-90°	804.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	804.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	797	
5°	779	73
15°	672	188
25°	541	244
35°	287	181
45°	94	77
55°	29	27
65°	10	10
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P203213

CATALOG NUMBER: LSR6B10D010BZ EC6B10208040 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	796.6
2.5°	794.3
5°	779.3
7.5°	757.5
10°	731.0
12.5°	702.3
15°	672.4
17.5°	639.1
20°	609.2
22.5°	578.2
25°	541.4
27.5°	490.8
30°	431.0
32.5°	360.9
35°	287.4
37.5°	225.3
40°	171.3
42.5°	127.6
45°	94.3
47.5°	69.0
50°	50.6
52.5°	37.9
55°	28.7
57.5°	21.8
60°	17.2
62.5°	12.6
65°	10.3
67.5°	8.0
70°	5.7
72.5°	4.6
75°	3.4
77.5°	2.3
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)