

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203661

Luminaire Tested: **LSR6B30D010BZ EC6B30508030 6LBNH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203661  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30508030 6LBNH1  
Description: PORTFOLIO 6IN CYLINDER  
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1858.7 lumens  
Efficiency: N/A  
Efficacy: 66.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203661

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBNH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203661

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBNH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203661

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBNH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	214.3	11.5
10°-20°	511.0	27.5
20°-30°	585.4	31.5
30°-40°	393.3	21.2
40°-50°	112.4	6.0
50°-60°	27.5	1.5
60°-70°	10.5	0.6
70°-80°	4.0	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1310.6	70.5
0°-40°	1703.9	91.7
0°-60°	1843.7	99.2
0°-90°	1858.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1858.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2383	
5°	2315	214
15°	1834	511
25°	1278	585
35°	627	393
45°	129	112
55°	30	27
65°	10	10
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P203661

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBNH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2382.6
2.5°	2365.7
5°	2314.9
7.5°	2223.3
10°	2111.5
12.5°	1969.2
15°	1833.6
17.5°	1691.2
20°	1548.9
22.5°	1413.3
25°	1277.7
27.5°	1152.3
30°	1006.6
32.5°	813.4
35°	627.0
37.5°	457.5
40°	315.2
42.5°	206.7
45°	128.8
47.5°	78.0
50°	47.4
52.5°	37.3
55°	30.5
57.5°	23.7
60°	16.9
62.5°	13.6
65°	10.2
67.5°	6.8
70°	6.8
72.5°	3.4
75°	3.4
77.5°	3.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)