

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204073

Luminaire Tested: **LSR6B30D010BZ EC6B30508030 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508030 6LBNMW1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2133.0 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204073

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204073

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																																				
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81																																				
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																																				
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66																																				
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61																																				
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56																																				
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																																				
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47																																				
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44																																				
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204073

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.4	7.6
10°-20°	430.5	20.2
20°-30°	574.8	26.9
30°-40°	463.7	21.7
40°-50°	222.3	10.4
50°-60°	131.8	6.2
60°-70°	87.6	4.1
70°-80°	46.9	2.2
80°-90°	12.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1167.8	54.7
0°-40°	1631.5	76.5
0°-60°	1985.6	93.1
0°-90°	2133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1749	
5°	1729	162
15°	1532	431
25°	1258	575
35°	742	464
45°	275	222
55°	146	132
65°	88	88
75°	44	47
85°	10	13
90°	0	



TEST NUMBER: P204073

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1749.2
2.5°	1749.2
5°	1728.9
7.5°	1695.0
10°	1647.5
12.5°	1596.7
15°	1532.3
17.5°	1471.2
20°	1403.4
22.5°	1332.3
25°	1257.7
27.5°	1179.7
30°	1067.8
32.5°	911.9
35°	742.4
37.5°	586.5
40°	454.3
42.5°	352.6
45°	274.6
47.5°	217.0
50°	183.1
52.5°	162.7
55°	145.8
57.5°	132.2
60°	115.3
62.5°	101.7
65°	88.1
67.5°	74.6
70°	64.4
72.5°	54.2
75°	44.1
77.5°	33.9
80°	27.1
82.5°	20.3
85°	10.2
87.5°	3.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)