

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205407

Luminaire Tested: **LSR6B30D010BZ EC6B30508030 6LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205407  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30508030 6LBSL11  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3185.9 lumens  
Efficiency: N/A  
Efficacy: 113.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205407

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205407

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205407

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	185.3	5.8
10°-20°	471.6	14.8
20°-30°	601.4	18.9
30°-40°	623.7	19.6
40°-50°	574.7	18.0
50°-60°	432.3	13.6
60°-70°	233.4	7.3
70°-80°	62.6	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1258.3	39.5
0°-40°	1882.0	59.1
0°-60°	2889.0	90.7
0°-90°	3185.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3185.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2010	
5°	1980	185
15°	1682	472
25°	1306	601
35°	995	624
45°	748	575
55°	484	432
65°	234	233
75°	54	63
85°	0	1
90°	0	



TEST NUMBER: P205407

CATALOG NUMBER: LSR6B30D010BZ EC6B30508030 6LBSLI1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2010.4
2.5°	2003.6
5°	1980.0
7.5°	1936.0
10°	1858.1
12.5°	1780.3
15°	1682.1
17.5°	1590.7
20°	1496.0
22.5°	1397.8
25°	1306.4
27.5°	1218.4
30°	1137.2
32.5°	1062.7
35°	995.1
37.5°	930.7
40°	869.8
42.5°	805.5
45°	748.0
47.5°	683.7
50°	619.4
52.5°	551.7
55°	484.0
57.5°	416.3
60°	352.0
62.5°	291.1
65°	233.5
67.5°	179.4
70°	132.0
72.5°	91.4
75°	54.2
77.5°	23.7
80°	6.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)