

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202703

Luminaire Tested: **LSR6B10D010BZ EC6B10209040 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209040 6LBWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 815.7 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202703

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202703

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41		
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202703

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.5	5.8
10°-20°	134.8	16.5
20°-30°	197.7	24.2
30°-40°	205.7	25.2
40°-50°	142.3	17.5
50°-60°	62.0	7.6
60°-70°	19.0	2.3
70°-80°	5.7	0.7
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.0	46.6
0°-40°	585.8	71.8
0°-60°	790.1	96.9
0°-90°	815.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	503	
5°	501	48
15°	479	135
25°	432	198
35°	333	206
45°	184	142
55°	67	62
65°	18	19
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P202703

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	503.1
2.5°	504.1
5°	501.0
7.5°	496.7
10°	491.5
12.5°	486.2
15°	478.8
17.5°	469.3
20°	458.7
22.5°	447.1
25°	432.3
27.5°	413.2
30°	388.9
32.5°	363.6
35°	332.9
37.5°	299.1
40°	260.0
42.5°	220.9
45°	183.9
47.5°	149.0
50°	118.4
52.5°	89.8
55°	66.6
57.5°	47.6
60°	32.8
62.5°	24.3
65°	18.0
67.5°	13.7
70°	9.5
72.5°	7.4
75°	5.3
77.5°	3.2
80°	2.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)