

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202806

Luminaire Tested: **LSR6B10D010BZ EC6B10209040 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209040 6LBWWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 843.1 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202806

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202806

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68		
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62		
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202806

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	6.0
10°-20°	149.7	17.8
20°-30°	225.3	26.7
30°-40°	230.4	27.3
40°-50°	139.9	16.6
50°-60°	39.4	4.7
60°-70°	6.0	0.7
70°-80°	2.0	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.3	50.4
0°-40°	655.7	77.8
0°-60°	835.0	99.0
0°-90°	843.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	843.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	524	
5°	526	50
15°	530	150
25°	492	225
35°	373	230
45°	180	140
55°	39	39
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P202806

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	523.7
2.5°	523.7
5°	525.8
7.5°	528.9
10°	528.9
12.5°	531.1
15°	530.0
17.5°	527.9
20°	520.5
22.5°	509.9
25°	491.9
27.5°	471.8
30°	444.3
32.5°	411.5
35°	373.4
37.5°	331.1
40°	282.5
42.5°	231.7
45°	179.8
47.5°	133.3
50°	94.2
52.5°	63.5
55°	39.1
57.5°	23.3
60°	11.6
62.5°	7.4
65°	5.3
67.5°	4.2
70°	3.2
72.5°	2.1
75°	2.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)