

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204967

Luminaire Tested: **LSR6B10D010BZ EC6B10208050 6LBSCMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204967  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10208050 6LBCSMMS1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1132.6 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204967

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P204967

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204967

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.0	4.3
10°-20°	137.5	12.1
20°-30°	200.9	17.7
30°-40°	229.7	20.3
40°-50°	220.8	19.5
50°-60°	170.5	15.1
60°-70°	95.2	8.4
70°-80°	27.7	2.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.4	34.2
0°-40°	617.2	54.5
0°-60°	1008.5	89.0
0°-90°	1132.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1132.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	520	
5°	516	49
15°	488	138
25°	437	201
35°	368	230
45°	288	221
55°	191	171
65°	95	95
75°	24	28
85°	1	1
90°	0	



TEST NUMBER: P204967

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	520.1
2.5°	520.1
5°	515.7
7.5°	513.5
10°	506.2
12.5°	497.4
15°	487.9
17.5°	478.3
20°	464.4
22.5°	453.4
25°	436.6
27.5°	419.7
30°	402.9
32.5°	386.0
35°	367.7
37.5°	349.4
40°	328.2
42.5°	309.1
45°	287.9
47.5°	263.7
50°	241.0
52.5°	216.1
55°	191.2
57.5°	165.6
60°	141.4
62.5°	117.2
65°	95.2
67.5°	74.7
70°	55.7
72.5°	38.8
75°	24.2
77.5°	12.5
80°	4.4
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)