

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203523

Luminaire Tested: **LSR6B10D010BZ EC6B10208050 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203523  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10208050 6LBMMW1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 883.1 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203523

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203523

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89																			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71																			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64																			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58																			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53																			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48																			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41																			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203523

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.9	6.9
10°-20°	163.1	18.5
20°-30°	218.9	24.8
30°-40°	179.6	20.3
40°-50°	107.8	12.2
50°-60°	71.7	8.1
60°-70°	48.0	5.4
70°-80°	25.9	2.9
80°-90°	7.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	442.9	50.1
0°-40°	622.4	70.5
0°-60°	801.9	90.8
0°-90°	883.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	883.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	659	
5°	648	61
15°	581	163
25°	482	219
35°	285	180
45°	136	108
55°	79	72
65°	49	48
75°	24	26
85°	6	7
90°	0	



TEST NUMBER: P203523

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	659.0
2.5°	654.1
5°	648.0
7.5°	634.6
10°	618.8
12.5°	599.3
15°	581.0
17.5°	559.1
20°	537.2
22.5°	512.8
25°	482.3
27.5°	445.8
30°	397.1
32.5°	342.3
35°	285.0
37.5°	236.3
40°	194.9
42.5°	162.0
45°	136.4
47.5°	115.7
50°	101.1
52.5°	88.9
55°	79.2
57.5°	70.6
60°	63.3
62.5°	54.8
65°	48.7
67.5°	41.4
70°	35.3
72.5°	29.2
75°	24.4
77.5°	19.5
80°	14.6
82.5°	11.0
85°	6.1
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)