

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204870

Luminaire Tested: **LSR6B10D010BZ EC6B10209050 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209050 6LBCSMB1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 859.5 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204870
CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204870

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75	75	75	75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65	65	65	65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56	56	56	56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49	49	49	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43	43	43	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39	39	39	39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35	35	35	35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31	31	31	31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28	28	28	28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204870

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.3	4.0
10°-20°	97.8	11.4
20°-30°	147.0	17.1
30°-40°	174.4	20.3
40°-50°	172.6	20.1
50°-60°	135.6	15.8
60°-70°	76.0	8.8
70°-80°	21.4	2.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.1	32.5
0°-40°	453.6	52.8
0°-60°	761.8	88.6
0°-90°	859.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	859.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	363	
5°	362	34
15°	347	98
25°	319	147
35°	280	174
45°	225	173
55°	153	136
65°	76	76
75°	18	21
85°	0	0
90°	0	



TEST NUMBER: P204870

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	362.9
2.5°	361.7
5°	362.3
7.5°	359.2
10°	355.5
12.5°	351.2
15°	346.9
17.5°	341.4
20°	334.0
22.5°	326.6
25°	319.2
27.5°	311.2
30°	300.7
32.5°	290.2
35°	279.7
37.5°	267.4
40°	253.2
42.5°	239.7
45°	224.9
47.5°	208.3
50°	191.0
52.5°	171.3
55°	152.8
57.5°	131.9
60°	112.1
62.5°	94.3
65°	75.8
67.5°	59.8
70°	44.4
72.5°	30.2
75°	18.5
77.5°	9.2
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)