

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205521

Luminaire Tested: **LSR6B30D010BZ EC6B30509730 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509730 6LBMGPH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1230.9 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205521

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205521

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																																				
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																																				
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																																				
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73																																				
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																																				
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																																				
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																																				
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																																				
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																																				
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205521

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	9.6
10°-20°	305.7	24.8
20°-30°	389.5	31.6
30°-40°	275.3	22.4
40°-50°	100.5	8.2
50°-60°	27.9	2.3
60°-70°	10.1	0.8
70°-80°	3.6	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	813.1	66.1
0°-40°	1088.4	88.4
0°-60°	1216.8	98.9
0°-90°	1230.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1230.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1283	
5°	1260	118
15°	1089	306
25°	865	390
35°	438	275
45°	122	101
55°	30	28
65°	10	10
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P205521

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1282.6
2.5°	1277.6
5°	1260.2
7.5°	1225.4
10°	1188.1
12.5°	1138.4
15°	1088.7
17.5°	1039.0
20°	989.3
22.5°	929.6
25°	865.0
27.5°	775.5
30°	676.1
32.5°	556.8
35°	437.5
37.5°	333.1
40°	243.6
42.5°	176.5
45°	121.8
47.5°	82.0
50°	54.7
52.5°	37.3
55°	29.8
57.5°	22.4
60°	17.4
62.5°	12.4
65°	9.9
67.5°	7.5
70°	5.0
72.5°	5.0
75°	2.5
77.5°	2.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)