

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204187

Luminaire Tested: **LSR6B30D010BZ EC6B30509730 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509730 6LBSH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2297.3 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204187

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204187

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204187

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.5	4.9
10°-20°	305.9	13.3
20°-30°	424.8	18.5
30°-40°	463.6	20.2
40°-50°	432.4	18.8
50°-60°	328.2	14.3
60°-70°	179.7	7.8
70°-80°	49.4	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.3	36.7
0°-40°	1306.8	56.9
0°-60°	2067.5	90.0
0°-90°	2297.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2297.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1202	
5°	1191	113
15°	1090	306
25°	923	425
35°	741	464
45°	562	432
55°	367	328
65°	180	180
75°	43	49
85°	0	1
90°	0	



TEST NUMBER: P204187

CATALOG NUMBER: LSR6B30D010BZ EC6B30509730 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1201.5
2.5°	1201.5
5°	1191.4
7.5°	1176.2
10°	1153.5
12.5°	1123.1
15°	1090.2
17.5°	1049.7
20°	1011.8
22.5°	966.3
25°	923.3
27.5°	880.3
30°	832.2
32.5°	786.7
35°	741.1
37.5°	695.6
40°	652.6
42.5°	607.1
45°	561.5
47.5°	516.0
50°	465.4
52.5°	417.4
55°	366.8
57.5°	318.7
60°	270.7
62.5°	222.6
65°	179.6
67.5°	139.1
70°	103.7
72.5°	70.8
75°	43.0
77.5°	20.2
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)