

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203639

Luminaire Tested: **LSR6B15D010BZ EC6B10209024 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209024 6LBNH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 666.5 lumens
Efficiency: N/A
Efficacy: 46.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203639

CATALOG NUMBER: LSR6B15D010BZ EC6B10209024 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203639

CATALOG NUMBER: LSR6B15D010BZ EC6B10209024 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203639

CATALOG NUMBER: LSR6B15D010BZ EC6B10209024 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	11.5
10°-20°	183.2	27.5
20°-30°	209.9	31.5
30°-40°	141.1	21.2
40°-50°	40.3	6.0
50°-60°	9.9	1.5
60°-70°	3.7	0.6
70°-80°	1.4	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.0	70.5
0°-40°	611.1	91.7
0°-60°	661.2	99.2
0°-90°	666.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	854	
5°	830	77
15°	658	183
25°	458	210
35°	225	141
45°	46	40
55°	11	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203639

CATALOG NUMBER: LSR6B15D010BZ EC6B10209024 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	854.5
2.5°	848.4
5°	830.2
7.5°	797.3
10°	757.2
12.5°	706.2
15°	657.6
17.5°	606.5
20°	555.5
22.5°	506.8
25°	458.2
27.5°	413.3
30°	361.0
32.5°	291.7
35°	224.9
37.5°	164.1
40°	113.0
42.5°	74.1
45°	46.2
47.5°	28.0
50°	17.0
52.5°	13.4
55°	10.9
57.5°	8.5
60°	6.1
62.5°	4.9
65°	3.6
67.5°	2.4
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)