

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205408

Luminaire Tested: **LSR6B30D010BZ EC6B30508035 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508035 6LBSL11
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3264.7 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205408

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205408

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205408

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.8	5.8
10°-20°	483.3	14.8
20°-30°	616.3	18.9
30°-40°	639.2	19.6
40°-50°	588.9	18.0
50°-60°	443.0	13.6
60°-70°	239.1	7.3
70°-80°	64.1	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1289.4	39.5
0°-40°	1928.6	59.1
0°-60°	2960.5	90.7
0°-90°	3264.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3264.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2060	
5°	2029	190
15°	1724	483
25°	1339	616
35°	1020	639
45°	766	589
55°	496	443
65°	239	239
75°	56	64
85°	0	1
90°	0	



TEST NUMBER: P205408

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2060.2
2.5°	2053.3
5°	2029.0
7.5°	1983.9
10°	1904.1
12.5°	1824.4
15°	1723.8
17.5°	1630.1
20°	1533.0
22.5°	1432.4
25°	1338.8
27.5°	1248.6
30°	1165.4
32.5°	1089.1
35°	1019.7
37.5°	953.8
40°	891.4
42.5°	825.5
45°	766.5
47.5°	700.6
50°	634.7
52.5°	565.3
55°	496.0
57.5°	426.6
60°	360.7
62.5°	298.3
65°	239.3
67.5°	183.8
70°	135.3
72.5°	93.6
75°	55.5
77.5°	24.3
80°	6.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)