

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204671

Luminaire Tested: **LSR6B15D010BZ EC6B10209024 6LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204671  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10209024 6LBPSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1189.4 lumens  
Efficiency: N/A  
Efficacy: 83.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204671

CATALOG NUMBER: LSR6B15D010BZ EC6B10209024 6LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204671

CATALOG NUMBER: LSR6B15D010BZ EC6B10209024 6LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204671

CATALOG NUMBER: LSR6B15D010BZ EC6B10209024 6LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.4	3.8
10°-20°	129.4	10.9
20°-30°	194.9	16.4
30°-40°	232.0	19.5
40°-50°	231.5	19.5
50°-60°	188.3	15.8
60°-70°	115.8	9.7
70°-80°	44.9	3.8
80°-90°	7.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.7	31.1
0°-40°	601.7	50.6
0°-60°	1021.5	85.9
0°-90°	1189.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1189.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	479	
5°	478	45
15°	460	129
25°	424	195
35°	371	232
45°	301	232
55°	211	188
65°	116	116
75°	41	45
85°	6	7
90°	0	



TEST NUMBER: P204671

CATALOG NUMBER: LSR6B15D010BZ EC6B10209024 6LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	479.2
2.5°	479.9
5°	477.8
7.5°	475.0
10°	471.4
12.5°	465.1
15°	459.5
17.5°	451.0
20°	441.8
22.5°	433.4
25°	424.2
27.5°	411.5
30°	398.9
32.5°	386.9
35°	371.4
37.5°	354.5
40°	339.0
42.5°	319.9
45°	300.9
47.5°	280.5
50°	258.6
52.5°	236.1
55°	210.7
57.5°	186.0
60°	162.1
62.5°	138.8
65°	116.3
67.5°	95.1
70°	75.4
72.5°	57.1
75°	40.9
77.5°	26.8
80°	16.2
82.5°	9.9
85°	5.6
87.5°	2.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)