

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202735

Luminaire Tested: **LSR6B30D010BZ EC6B30508035 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508035 6LBWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2678.4 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202735

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202735

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																												
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																												
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																												
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																												
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																												
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																												
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																												
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																												
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																												
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202735

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.0	5.8
10°-20°	442.7	16.5
20°-30°	649.1	24.2
30°-40°	675.6	25.2
40°-50°	467.5	17.5
50°-60°	203.5	7.6
60°-70°	62.4	2.3
70°-80°	18.7	0.7
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1247.9	46.6
0°-40°	1923.5	71.8
0°-60°	2594.5	96.9
0°-90°	2678.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2678.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1652	
5°	1645	156
15°	1572	443
25°	1420	649
35°	1093	676
45°	604	467
55°	219	203
65°	59	62
75°	17	19
85°	4	3
90°	0	



TEST NUMBER: P202735

CATALOG NUMBER: LSR6B30D010BZ EC6B30508035 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1652.0
2.5°	1655.5
5°	1645.1
7.5°	1631.2
10°	1613.8
12.5°	1596.5
15°	1572.2
17.5°	1541.0
20°	1506.2
22.5°	1468.1
25°	1419.5
27.5°	1357.0
30°	1277.2
32.5°	1193.9
35°	1093.2
37.5°	982.2
40°	853.8
42.5°	725.4
45°	603.9
47.5°	489.4
50°	388.7
52.5°	295.0
55°	218.6
57.5°	156.2
60°	107.6
62.5°	79.8
65°	59.0
67.5°	45.1
70°	31.2
72.5°	24.3
75°	17.4
77.5°	10.4
80°	6.9
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)