

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204906

Luminaire Tested: **LSR6B30D010BZ EC6B30509035 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509035 6LBCSMB1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2375.6 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204906

CATALOG NUMBER: LSR6B30D010BZ EC6B30509035 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204906

CATALOG NUMBER: LSR6B30D010BZ EC6B30509035 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88						88													
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75						75													
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65						65													
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56						56													
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49						49													
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43						43													
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39						39													
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35						35													
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31						31													
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28						28													

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204906

CATALOG NUMBER: LSR6B30D010BZ EC6B30509035 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	4.0
10°-20°	270.3	11.4
20°-30°	406.3	17.1
30°-40°	482.1	20.3
40°-50°	477.1	20.1
50°-60°	374.8	15.8
60°-70°	210.1	8.8
70°-80°	59.0	2.5
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	771.5	32.5
0°-40°	1253.7	52.8
0°-60°	2105.6	88.6
0°-90°	2375.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2375.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1003	
5°	1001	95
15°	959	270
25°	882	406
35°	773	482
45°	622	477
55°	422	375
65°	210	210
75°	51	59
85°	0	1
90°	0	



TEST NUMBER: P204906

CATALOG NUMBER: LSR6B30D010BZ EC6B30509035 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1003.1
2.5°	999.7
5°	1001.4
7.5°	992.9
10°	982.7
12.5°	970.8
15°	958.8
17.5°	943.5
20°	923.1
22.5°	902.6
25°	882.2
27.5°	860.1
30°	831.1
32.5°	802.2
35°	773.2
37.5°	739.1
40°	700.0
42.5°	662.5
45°	621.6
47.5°	575.6
50°	528.0
52.5°	473.5
55°	422.4
57.5°	364.5
60°	310.0
62.5°	260.6
65°	209.5
67.5°	165.2
70°	122.6
72.5°	83.5
75°	51.1
77.5°	25.5
80°	6.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)