

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205483

Luminaire Tested: **LSR6B15D010BZ EC6B10208027 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208027 6LBMGPH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 782.8 lumens
Efficiency: N/A
Efficacy: 54.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205483

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205483

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																			
3	102	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79																			
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205483

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	9.6
10°-20°	194.4	24.8
20°-30°	247.7	31.6
30°-40°	175.1	22.4
40°-50°	63.9	8.2
50°-60°	17.7	2.3
60°-70°	6.4	0.8
70°-80°	2.3	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.1	66.1
0°-40°	692.2	88.4
0°-60°	773.8	98.9
0°-90°	782.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	782.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	816	
5°	801	75
15°	692	194
25°	550	248
35°	278	175
45°	78	64
55°	19	18
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205483

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	815.6
2.5°	812.5
5°	801.4
7.5°	779.3
10°	755.6
12.5°	724.0
15°	692.4
17.5°	660.7
20°	629.1
22.5°	591.2
25°	550.1
27.5°	493.2
30°	430.0
32.5°	354.1
35°	278.2
37.5°	211.8
40°	154.9
42.5°	112.2
45°	77.5
47.5°	52.2
50°	34.8
52.5°	23.7
55°	19.0
57.5°	14.2
60°	11.1
62.5°	7.9
65°	6.3
67.5°	4.7
70°	3.2
72.5°	3.2
75°	1.6
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)