

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204803

Luminaire Tested: **LSR6B30D010BZ EC6B30509035 6LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204803  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30509035 6LBCSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2811.6 lumens  
Efficiency: N/A  
Efficacy: 100.4 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204803

CATALOG NUMBER: LSR6B30D010BZ EC6B30509035 6LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204803

CATALOG NUMBER: LSR6B30D010BZ EC6B30509035 6LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204803

CATALOG NUMBER: LSR6B30D010BZ EC6B30509035 6LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.8	3.9
10°-20°	309.7	11.0
20°-30°	466.0	16.6
30°-40°	552.2	19.6
40°-50°	549.6	19.5
50°-60°	443.0	15.8
60°-70°	268.0	9.5
70°-80°	99.5	3.5
80°-90°	14.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	884.5	31.5
0°-40°	1436.7	51.1
0°-60°	2429.3	86.4
0°-90°	2811.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2811.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1148	
5°	1143	109
15°	1097	310
25°	1012	466
35°	884	552
45°	716	550
55°	494	443
65°	269	268
75°	90	100
85°	12	15
90°	0	



TEST NUMBER: P204803

CATALOG NUMBER: LSR6B30D010BZ EC6B30509035 6LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1148.3
2.5°	1148.3
5°	1143.2
7.5°	1139.8
10°	1129.6
12.5°	1112.6
15°	1097.2
17.5°	1080.2
20°	1059.7
22.5°	1039.3
25°	1012.0
27.5°	983.1
30°	950.7
32.5°	920.0
35°	884.3
37.5°	846.8
40°	802.5
42.5°	759.9
45°	715.6
47.5°	666.2
50°	611.7
52.5°	555.4
55°	494.1
57.5°	439.6
60°	378.2
62.5°	323.7
65°	269.2
67.5°	218.1
70°	170.4
72.5°	127.8
75°	90.3
77.5°	57.9
80°	34.1
82.5°	20.4
85°	11.9
87.5°	5.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)