

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202610

Luminaire Tested: **LSR6B15D010BZ EC6B10209027 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209027 6LBMWMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 944.9 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202610

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202610

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																	
	1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93	93	93	93	93	93	93	93	93	93	93																	
	2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86	86	86	86	86	86	86	86																	
	3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80	80	80	80	80	80	80	80																	
	4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74	74	74	74	74	74	74	74																	
	5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69	69	69	69	69	69	69	69	69	69	69																	
	6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64	64	64	64	64	64	64	64	64	64	64																	
	7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60	60	60	60	60	60	60	60	60	60	60																	
	8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56	56	56	56	56	56	56	56	56	56	56																	
	9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53	53	53	53	53	53	53	53	53	53	53																	
	10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50	50	50	50	50	50	50	50	50	50	50																	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202610

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	10.2
10°-20°	247.6	26.2
20°-30°	304.1	32.2
30°-40°	208.5	22.1
40°-50°	67.0	7.1
50°-60°	13.6	1.4
60°-70°	5.3	0.6
70°-80°	2.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	648.1	68.6
0°-40°	856.7	90.7
0°-60°	937.3	99.2
0°-90°	944.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	944.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1051	
5°	1031	96
15°	886	248
25°	671	304
35°	333	209
45°	79	67
55°	14	14
65°	6	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P202610

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1050.9
2.5°	1044.4
5°	1030.8
7.5°	1005.2
10°	970.7
12.5°	928.2
15°	885.7
17.5°	838.4
20°	786.3
22.5°	731.8
25°	670.9
27.5°	603.6
30°	518.6
32.5°	424.8
35°	332.7
37.5°	248.5
40°	178.8
42.5°	121.8
45°	79.4
47.5°	48.9
50°	29.7
52.5°	18.4
55°	13.6
57.5°	10.4
60°	8.0
62.5°	6.4
65°	5.6
67.5°	4.0
70°	3.2
72.5°	2.4
75°	1.6
77.5°	1.6
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)