

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204672

Luminaire Tested: **LSR6B15D010BZ EC6B10209027 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209027 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1351.8 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204672

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204672

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204672

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	3.8
10°-20°	147.1	10.9
20°-30°	221.6	16.4
30°-40°	263.6	19.5
40°-50°	263.1	19.5
50°-60°	214.0	15.8
60°-70°	131.7	9.7
70°-80°	51.0	3.8
80°-90°	8.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.3	31.1
0°-40°	683.9	50.6
0°-60°	1161.0	85.9
0°-90°	1351.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1351.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	545	
5°	543	52
15°	522	147
25°	482	222
35°	422	264
45°	342	263
55°	240	214
65°	132	132
75°	46	51
85°	6	8
90°	0	



TEST NUMBER: P204672

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	544.7
2.5°	545.5
5°	543.1
7.5°	539.8
10°	535.8
12.5°	528.6
15°	522.2
17.5°	512.6
20°	502.2
22.5°	492.6
25°	482.2
27.5°	467.8
30°	453.3
32.5°	439.7
35°	422.1
37.5°	402.9
40°	385.3
42.5°	363.6
45°	342.0
47.5°	318.8
50°	294.0
52.5°	268.3
55°	239.5
57.5°	211.5
60°	184.2
62.5°	157.8
65°	132.2
67.5°	108.1
70°	85.7
72.5°	64.9
75°	46.5
77.5°	30.4
80°	18.4
82.5°	11.2
85°	6.4
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)