

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205004

Luminaire Tested: **LSR6B30D010BZ EC6B30508040 6LBSCMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30508040 6LBCSMMS1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3148.2 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205004

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P205004

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205004

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.2	4.3
10°-20°	382.3	12.1
20°-30°	558.4	17.7
30°-40°	638.7	20.3
40°-50°	613.8	19.5
50°-60°	474.0	15.1
60°-70°	264.5	8.4
70°-80°	77.0	2.4
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.9	34.2
0°-40°	1715.6	54.5
0°-60°	2803.3	89.0
0°-90°	3148.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3148.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1446	
5°	1434	136
15°	1356	382
25°	1214	558
35°	1022	639
45°	800	614
55°	532	474
65°	265	265
75°	67	77
85°	2	3
90°	0	



TEST NUMBER: P205004

CATALOG NUMBER: LSR6B30D010BZ EC6B30508040 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1445.7
2.5°	1445.7
5°	1433.5
7.5°	1427.4
10°	1407.0
12.5°	1382.6
15°	1356.1
17.5°	1329.7
20°	1291.0
22.5°	1260.4
25°	1213.6
27.5°	1166.8
30°	1119.9
32.5°	1073.1
35°	1022.2
37.5°	971.3
40°	912.2
42.5°	859.3
45°	800.2
47.5°	733.0
50°	669.9
52.5°	600.7
55°	531.5
57.5°	460.2
60°	393.0
62.5°	325.8
65°	264.7
67.5°	207.7
70°	154.8
72.5°	107.9
75°	67.2
77.5°	34.6
80°	12.2
82.5°	4.1
85°	2.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)