

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204883

Luminaire Tested: **LSR6B15D010BZ EC6B10209727 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209727 6LBCSMB1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 971.6 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204883

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204883

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88																
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75																
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65																
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56																
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49																
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43																
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39																
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35																
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31																
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204883

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.8	4.0
10°-20°	110.6	11.4
20°-30°	166.2	17.1
30°-40°	197.2	20.3
40°-50°	195.1	20.1
50°-60°	153.3	15.8
60°-70°	86.0	8.8
70°-80°	24.1	2.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.6	32.5
0°-40°	512.7	52.8
0°-60°	861.1	88.6
0°-90°	971.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	971.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	410	
5°	410	39
15°	392	111
25°	361	166
35°	316	197
45°	254	195
55°	173	153
65°	86	86
75°	21	24
85°	0	0
90°	0	



TEST NUMBER: P204883

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	410.3
2.5°	408.9
5°	409.6
7.5°	406.1
10°	401.9
12.5°	397.0
15°	392.2
17.5°	385.9
20°	377.5
22.5°	369.2
25°	360.8
27.5°	351.8
30°	339.9
32.5°	328.1
35°	316.2
37.5°	302.3
40°	286.3
42.5°	271.0
45°	254.2
47.5°	235.4
50°	215.9
52.5°	193.6
55°	172.7
57.5°	149.1
60°	126.8
62.5°	106.6
65°	85.7
67.5°	67.6
70°	50.2
72.5°	34.1
75°	20.9
77.5°	10.4
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)