

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204907

Luminaire Tested: **LSR6B30D010BZ EC6B30509040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B30D010BZ EC6B30509040 6LBCSMB1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2379.6 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204907

CATALOG NUMBER: LSR6B30D010BZ EC6B30509040 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204907

CATALOG NUMBER: LSR6B30D010BZ EC6B30509040 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88																
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75																
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65																
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56																
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49																
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43																
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39																
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35																
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31																
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204907

CATALOG NUMBER: LSR6B30D010BZ EC6B30509040 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.0	4.0
10°-20°	270.8	11.4
20°-30°	407.0	17.1
30°-40°	483.0	20.3
40°-50°	477.9	20.1
50°-60°	375.4	15.8
60°-70°	210.5	8.8
70°-80°	59.1	2.5
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	772.8	32.5
0°-40°	1255.8	52.8
0°-60°	2109.1	88.6
0°-90°	2379.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2379.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1005	
5°	1003	95
15°	960	271
25°	884	407
35°	774	483
45°	623	478
55°	423	375
65°	210	210
75°	51	59
85°	0	1
90°	0	



TEST NUMBER: P204907

CATALOG NUMBER: LSR6B30D010BZ EC6B30509040 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1004.8
2.5°	1001.4
5°	1003.1
7.5°	994.6
10°	984.3
12.5°	972.4
15°	960.5
17.5°	945.1
20°	924.6
22.5°	904.2
25°	883.7
27.5°	861.5
30°	832.5
32.5°	803.5
35°	774.5
37.5°	740.4
40°	701.2
42.5°	663.6
45°	622.7
47.5°	576.6
50°	528.8
52.5°	474.3
55°	423.1
57.5°	365.1
60°	310.5
62.5°	261.0
65°	209.8
67.5°	165.5
70°	122.8
72.5°	83.6
75°	51.2
77.5°	25.6
80°	6.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)