

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203641

Luminaire Tested: **LSR6B15D010BZ EC6B10209030 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209030 6LBNH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 787.8 lumens
Efficiency: N/A
Efficacy: 55.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203641

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203641

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203641

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	11.5
10°-20°	216.6	27.5
20°-30°	248.1	31.5
30°-40°	166.7	21.2
40°-50°	47.6	6.0
50°-60°	11.7	1.5
60°-70°	4.4	0.6
70°-80°	1.7	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.5	70.5
0°-40°	722.2	91.7
0°-60°	781.5	99.2
0°-90°	787.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1010	
5°	981	91
15°	777	217
25°	542	248
35°	266	167
45°	55	48
55°	13	12
65°	4	4
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P203641

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1009.9
2.5°	1002.7
5°	981.2
7.5°	942.4
10°	895.0
12.5°	834.6
15°	777.2
17.5°	716.8
20°	656.5
22.5°	599.0
25°	541.6
27.5°	488.4
30°	426.7
32.5°	344.8
35°	265.8
37.5°	193.9
40°	133.6
42.5°	87.6
45°	54.6
47.5°	33.0
50°	20.1
52.5°	15.8
55°	12.9
57.5°	10.1
60°	7.2
62.5°	5.7
65°	4.3
67.5°	2.9
70°	2.9
72.5°	1.4
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)