

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204259

Luminaire Tested: **LSR6B15D010BZ EC6B10209030 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209030 6LBSWH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1311.6 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204259

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204259

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204259

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.1	5.5
10°-20°	186.7	14.2
20°-30°	244.2	18.6
30°-40°	258.6	19.7
40°-50°	241.2	18.4
50°-60°	182.7	13.9
60°-70°	99.0	7.5
70°-80°	26.6	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	503.1	38.4
0°-40°	761.8	58.1
0°-60°	1185.7	90.4
0°-90°	1311.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1311.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	782	
5°	771	72
15°	667	187
25°	531	244
35°	413	259
45°	314	241
55°	205	183
65°	99	99
75°	23	27
85°	0	0
90°	0	



TEST NUMBER: P204259

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	782.2
2.5°	779.3
5°	770.7
7.5°	752.1
10°	727.7
12.5°	699.0
15°	667.4
17.5°	631.5
20°	599.9
22.5°	564.1
25°	531.0
27.5°	498.0
30°	466.5
32.5°	439.2
35°	413.4
37.5°	387.5
40°	363.1
42.5°	338.7
45°	314.3
47.5°	287.1
50°	259.8
52.5°	232.5
55°	205.2
57.5°	176.5
60°	149.3
62.5°	123.4
65°	99.0
67.5°	76.1
70°	56.0
72.5°	38.8
75°	23.0
77.5°	10.0
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)