

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203664

Luminaire Tested: **LSR6B30D010BZ EC6B30508050 6LBNH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203664  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30508050 6LBNH1  
Description: PORTFOLIO 6IN CYLINDER  
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1924.2 lumens  
Efficiency: N/A  
Efficacy: 68.7 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203664

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBNH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203664

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBNH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203664

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBNH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.8	11.5
10°-20°	529.0	27.5
20°-30°	606.0	31.5
30°-40°	407.2	21.2
40°-50°	116.3	6.0
50°-60°	28.5	1.5
60°-70°	10.8	0.6
70°-80°	4.2	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1356.8	70.5
0°-40°	1764.0	91.7
0°-60°	1908.8	99.2
0°-90°	1924.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1924.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2467	
5°	2396	222
15°	1898	529
25°	1323	606
35°	649	407
45°	133	116
55°	32	28
65°	10	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P203664

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBNH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2466.6
2.5°	2449.1
5°	2396.5
7.5°	2301.7
10°	2185.9
12.5°	2038.6
15°	1898.2
17.5°	1750.9
20°	1603.5
22.5°	1463.1
25°	1322.8
27.5°	1193.0
30°	1042.1
32.5°	842.1
35°	649.1
37.5°	473.7
40°	326.3
42.5°	214.0
45°	133.3
47.5°	80.7
50°	49.1
52.5°	38.6
55°	31.6
57.5°	24.6
60°	17.5
62.5°	14.0
65°	10.5
67.5°	7.0
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)