

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205495

Luminaire Tested: **LSR6B15D010BZ EC6B10209730 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209730 6LBMGPH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 610.4 lumens
Efficiency: N/A
Efficacy: 42.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205495

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBMGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P205495

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205495

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.4	9.6
10°-20°	151.6	24.8
20°-30°	193.2	31.6
30°-40°	136.6	22.4
40°-50°	49.8	8.2
50°-60°	13.8	2.3
60°-70°	5.0	0.8
70°-80°	1.8	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.3	66.1
0°-40°	539.8	88.4
0°-60°	603.5	98.9
0°-90°	610.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	610.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	636	
5°	625	58
15°	540	152
25°	429	193
35°	217	137
45°	60	50
55°	15	14
65°	5	5
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P205495

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	636.1
2.5°	633.7
5°	625.1
7.5°	607.8
10°	589.3
12.5°	564.6
15°	540.0
17.5°	515.3
20°	490.7
22.5°	461.1
25°	429.0
27.5°	384.6
30°	335.3
32.5°	276.2
35°	217.0
37.5°	165.2
40°	120.8
42.5°	87.5
45°	60.4
47.5°	40.7
50°	27.1
52.5°	18.5
55°	14.8
57.5°	11.1
60°	8.6
62.5°	6.2
65°	4.9
67.5°	3.7
70°	2.5
72.5°	2.5
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)