

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204076

Luminaire Tested: **LSR6B30D010BZ EC6B30508050 6LBNMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204076  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B30D010BZ EC6B30508050 6LBNMW1  
Description: PORTFOLIO 6IN CYLINDER  
NARROW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2208.1 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204076

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBNMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204076

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBNMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																																			
	2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81																																			
	3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																																			
	4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66																																			
	5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61																																			
	6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56																																			
	7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																																			
	8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47																																			
	9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44																																			
	10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41																																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204076

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBNMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.2	7.6
10°-20°	445.7	20.2
20°-30°	595.1	26.9
30°-40°	480.1	21.7
40°-50°	230.1	10.4
50°-60°	136.4	6.2
60°-70°	90.7	4.1
70°-80°	48.6	2.2
80°-90°	13.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1209.0	54.7
0°-40°	1689.0	76.5
0°-60°	2055.5	93.1
0°-90°	2208.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2208.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1811	
5°	1790	168
15°	1586	446
25°	1302	595
35°	769	480
45°	284	230
55°	151	136
65°	91	91
75°	46	49
85°	10	13
90°	0	



TEST NUMBER: P204076

CATALOG NUMBER: LSR6B30D010BZ EC6B30508050 6LBNMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1810.9
2.5°	1810.9
5°	1789.8
7.5°	1754.7
10°	1705.6
12.5°	1653.0
15°	1586.3
17.5°	1523.1
20°	1452.9
22.5°	1379.2
25°	1302.0
27.5°	1221.3
30°	1105.5
32.5°	944.0
35°	768.6
37.5°	607.1
40°	470.3
42.5°	365.0
45°	284.3
47.5°	224.6
50°	189.5
52.5°	168.5
55°	150.9
57.5°	136.9
60°	119.3
62.5°	105.3
65°	91.2
67.5°	77.2
70°	66.7
72.5°	56.2
75°	45.6
77.5°	35.1
80°	28.1
82.5°	21.1
85°	10.5
87.5°	3.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)