

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203749

Luminaire Tested: **LSR6B15D010BZ EC6B10209730 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203749
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209730 6LBNWH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 737.1 lumens
Efficiency: N/A
Efficacy: 51.5 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203749

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203749

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66																			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63																			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60																			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203749

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	16.6
10°-20°	235.4	31.9
20°-30°	214.0	29.0
30°-40°	129.7	17.6
40°-50°	29.5	4.0
50°-60°	3.8	0.5
60°-70°	1.7	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	571.9	77.6
0°-40°	701.6	95.2
0°-60°	734.9	99.7
0°-90°	737.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	737.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1447	
5°	1364	123
15°	848	235
25°	464	214
35°	206	130
45°	33	30
55°	4	4
65°	1	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203749

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBNWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1447.1
2.5°	1429.6
5°	1364.4
7.5°	1259.0
10°	1124.8
12.5°	985.6
15°	847.7
17.5°	722.3
20°	617.0
22.5°	531.7
25°	464.0
27.5°	403.8
30°	344.9
32.5°	275.9
35°	205.7
37.5°	144.2
40°	95.3
42.5°	58.9
45°	32.6
47.5°	15.0
50°	6.3
52.5°	5.0
55°	3.8
57.5°	3.8
60°	2.5
62.5°	2.5
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)