

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204367

Luminaire Tested: **LSR6B15D010BZ EC6B10209730 6LBSGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204367  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10209730 6LBSGPH1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1045.4 lumens  
Efficiency: N/A  
Efficacy: 73.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204367

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBSGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204367

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBSGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204367

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBSGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.7	4.4
10°-20°	128.3	12.3
20°-30°	187.2	17.9
30°-40°	213.4	20.4
40°-50°	204.7	19.6
50°-60°	156.8	15.0
60°-70°	86.0	8.2
70°-80°	22.9	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.2	34.5
0°-40°	574.6	55.0
0°-60°	936.2	89.5
0°-90°	1045.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1045.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	486	
5°	482	46
15°	455	128
25°	406	187
35°	341	213
45°	266	205
55°	176	157
65°	87	86
75°	20	23
85°	0	0
90°	0	



TEST NUMBER: P204367

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBSGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	485.6
2.5°	484.3
5°	481.8
7.5°	478.0
10°	473.0
12.5°	464.2
15°	455.4
17.5°	445.4
20°	434.1
22.5°	420.3
25°	406.5
27.5°	392.7
30°	375.1
32.5°	358.8
35°	341.3
37.5°	323.7
40°	306.1
42.5°	287.3
45°	266.0
47.5°	244.7
50°	222.1
52.5°	198.2
55°	175.7
57.5°	153.1
60°	129.2
62.5°	106.6
65°	86.6
67.5°	66.5
70°	48.9
72.5°	32.6
75°	20.1
77.5°	8.8
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)