

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204574

Luminaire Tested: **LSR6B15D010BZ EC6B10209730 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209730 6LBSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1227.9 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204574

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204574

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204574

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.9	3.8
10°-20°	133.6	10.9
20°-30°	201.3	16.4
30°-40°	239.5	19.5
40°-50°	239.0	19.5
50°-60°	194.4	15.8
60°-70°	119.6	9.7
70°-80°	46.3	3.8
80°-90°	7.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.8	31.1
0°-40°	621.2	50.6
0°-60°	1054.6	85.9
0°-90°	1227.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1227.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	495	
5°	493	47
15°	474	134
25°	438	201
35°	383	239
45°	311	239
55°	218	194
65°	120	120
75°	42	46
85°	6	7
90°	0	



TEST NUMBER: P204574

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	494.7
2.5°	495.5
5°	493.3
7.5°	490.4
10°	486.7
12.5°	480.2
15°	474.4
17.5°	465.6
20°	456.2
22.5°	447.5
25°	438.0
27.5°	424.9
30°	411.8
32.5°	399.4
35°	383.4
37.5°	366.0
40°	350.0
42.5°	330.3
45°	310.7
47.5°	289.6
50°	267.0
52.5°	243.7
55°	217.5
57.5°	192.1
60°	167.3
62.5°	143.3
65°	120.0
67.5°	98.2
70°	77.8
72.5°	58.9
75°	42.2
77.5°	27.6
80°	16.7
82.5°	10.2
85°	5.8
87.5°	2.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)