

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P201217

Luminaire Tested: **LSR6B15D010BZ EC6B10208035 6LBN1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P201217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35135)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208035 6LBN1LI
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1195.0 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 1.12' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P201217

CATALOG NUMBER: LSR6B15D010BZ EC6B10208035 6LBN1LI

Luminous Intensity Polar Plot





TEST NUMBER: P201217

CATALOG NUMBER: LSR6B15D010BZ EC6B10208035 6LBN1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89				89
3	105	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	85				85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80				80
5	96	88	83	79	94	87	83	79	86	82	78	84	80	78	83	80	77	76				76
6	92	84	79	75	90	83	78	74	82	77	74	80	76	74	79	76	73	72				72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68				68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65				65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62				62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59				59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29333
5°	27458
10°	22408
15°	16462
20°	11446
25°	8460
30°	6342
35°	3957
40°	1931
45°	677
50°	101
55°	76
60°	43
65°	26
70°	32
75°	0
80°	0
85°	0



TEST NUMBER: P201217

CATALOG NUMBER: LSR6B15D010BZ EC6B10208035 6LBN1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.1	18.8
10°-20°	406.1	34.0
20°-30°	329.0	27.5
30°-40°	189.0	15.8
40°-50°	40.4	3.4
50°-60°	3.6	0.3
60°-70°	1.4	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	960.3	80.4
0°-40°	1149.2	96.2
0°-60°	1193.2	99.9
0°-90°	1195.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1195.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2709	
5°	2526	225
15°	1468	406
25°	708	329
35°	299	189
45°	44	40
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P201217

CATALOG NUMBER: LSR6B15D010BZ EC6B10208035 6LBN1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2708.8
2.5°	2665.6
5°	2526.0
7.5°	2302.0
10°	2037.9
12.5°	1762.7
15°	1468.4
17.5°	1203.3
20°	993.3
22.5°	834.6
25°	708.1
27.5°	605.6
30°	507.2
32.5°	404.8
35°	299.3
37.5°	206.9
40°	136.6
42.5°	82.4
45°	44.2
47.5°	18.1
50°	6.0
52.5°	5.0
55°	4.0
57.5°	3.0
60°	2.0
62.5°	2.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)