

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203431

Luminaire Tested: **LSR6B15D010BZ EC6B10208040 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208040 6LBMB1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 661.3 lumens
Efficiency: N/A
Efficacy: 46.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203431

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P203431

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	11.4
10°-20°	186.4	28.2
20°-30°	224.5	33.9
30°-40°	142.0	21.5
40°-50°	32.5	4.9
50°-60°	0.4	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.4	73.6
0°-40°	628.4	95.0
0°-60°	661.3	100.0
0°-90°	661.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	661.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	832	
5°	814	76
15°	665	186
25°	497	224
35°	224	142
45°	36	33
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203431

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	832.5
2.5°	829.0
5°	813.7
7.5°	784.6
10°	748.7
12.5°	706.0
15°	664.9
17.5°	625.6
20°	584.6
22.5°	543.6
25°	497.4
27.5°	442.7
30°	376.1
32.5°	300.8
35°	223.9
37.5°	159.0
40°	107.7
42.5°	66.7
45°	35.9
47.5°	15.4
50°	3.4
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)