

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203673

Luminaire Tested: **LSR6B40D010BZ EC6B30508027 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508027 6LBNH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2513.7 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203673

CATALOG NUMBER: LSR6B40D010BZ EC6B30508027 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203673

CATALOG NUMBER: LSR6B40D010BZ EC6B30508027 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																																			
	2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																																			
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																																			
	4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																																			
	5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																																			
	6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																																			
	7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																																			
	8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																																			
	9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54																																			
	10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203673

CATALOG NUMBER: LSR6B40D010BZ EC6B30508027 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.8	11.5
10°-20°	691.0	27.5
20°-30°	791.6	31.5
30°-40°	531.9	21.2
40°-50°	152.0	6.0
50°-60°	37.2	1.5
60°-70°	14.1	0.6
70°-80°	5.5	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1772.4	70.5
0°-40°	2304.3	91.7
0°-60°	2493.5	99.2
0°-90°	2513.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2513.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3222	
5°	3130	290
15°	2480	691
25°	1728	792
35°	848	532
45°	174	152
55°	41	37
65°	14	14
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P203673

CATALOG NUMBER: LSR6B40D010BZ EC6B30508027 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3222.2
2.5°	3199.3
5°	3130.5
7.5°	3006.8
10°	2855.5
12.5°	2663.0
15°	2479.7
17.5°	2287.2
20°	2094.7
22.5°	1911.3
25°	1728.0
27.5°	1558.4
30°	1361.3
32.5°	1100.0
35°	847.9
37.5°	618.8
40°	426.3
42.5°	279.6
45°	174.2
47.5°	105.4
50°	64.2
52.5°	50.4
55°	41.3
57.5°	32.1
60°	22.9
62.5°	18.3
65°	13.8
67.5°	9.2
70°	9.2
72.5°	4.6
75°	4.6
77.5°	4.6
80°	4.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)